



MASTER TL-D Xtreme Secura

MASTER TL-D Xtreme Secura 58W/840 SLV/25

This TL-D Xtreme lamp has a protective coating that keeps glass and lamp components together in the event of accidental breakage. The lamp is easily identifiable by a blue ring at one end. Application areas are all places where glass shatters can disturb operations and can have an impact on product and people safety, e.g. the food and beverage industry. The lamp has a Teflon coating. It is compliant with HACCP regulations.

Warnings and Safety

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- In order to ensure the integrity of the coating, it is strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Product data


General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	86 lm/W	
Life to 50% Failures (Nom)	47,000 hour(s)	Color rendering index (CRI)	
		>80	
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power Consumption	58.5 W
Luminous Flux	5,000 lm	Lamp Current (Nom)	0.665 A
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4000 K		

MASTER TL-D Xtreme Secura

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	68 kWh
Product Data	
Order product name	MASTER TL-D Xtreme Secura 58W/840 SLV/25


Full product name	MASTER TL-D Xtreme Secura 58W/840 SLV/25
Full product code	871150088987440
Order code	927983784074
Material Nr. (12NC)	927983784074
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500889874
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500889881

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtreme Secura 58W/840 SLV/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm


Photometric data




Spectral Power Distribution Colour - MASTER TL-D Xtreme Secura 58W/840 SLV/25

MASTER TL-D Xtreme Secura

Lifetime




Life Expectancy Diagram - MASTER TL-D Xtreme Secura 58W/840 SLV/25



Life Expectancy Diagram - MASTER TL-D Xtreme Secura 58W/840 SLV/25

Life Expectancy Diagram - MASTER TL-D Xtreme Secura 58W/840 SLV/25



Lumen Maintenance Diagram - MASTER TL-D Xtreme Secura 58W/840 SLV/25

