



MASTER TL5 High Output TOP

MASTER TL5 HO TOP 54W/840 1SL/20

This TL5 HO lamp (tube diameter 16 mm) offers a constant light level, independent of temperature fluctuations, making it an excellent solution for warm applications. The TL5 HO TOP can be operated on equivalent systems as MASTER TL5 HO. Excellent solution for warm applications, such as unconditioned warehouses, wall washers, etc.

Warnings and Safety

- Not recommended for emergency lighting due to slower run-up behaviour than non-amalgam TL5 lamps

Product data

General Information		Controls and Dimming	
Cap-Base	G5 [G5]	Dimmable	Yes
Features	na [Not Applicable]		
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Shape	T5 [16 mm (T5)]
Luminous Flux	5,000 lm		
Color Designation	Cool White (CW)	Approval and Application	
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Nom)	2.2 mg
Luminous Efficacy (rated) (Nom)	88 lm/W	Energy Consumption kWh/1000 h	59 kWh
Color rendering index (CRI)	85		
Operating and Electrical		Product Data	
Power Consumption	54.1 W	Order product name	MASTER TL5 HO TOP 54W/840 1SL/20
Lamp Current (Nom)	0.455 A	Full product name	MASTER TL5 HO TOP 54W/840 1SL/20
		Full product code	871150026695805
		Order code	927993284041
		Material Nr. (12NC)	927993284041
		Numerator - Quantity Per Pack	1

MASTER TL5 High Output TOP


EAN/UPC - Product/Case	8711500266958
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500266965

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO TOP 54W/840 1SL/20	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO TOP 54W/840 1SL/20

Lifetime




Life Expectancy Diagram - MASTER TL5 HO TOP 54W/840 1SL/20



Life Expectancy Diagram - MASTER TL5 HO TOP 54W/840 1SL/20

MASTER TL5 High Output TOP

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO TOP 54W/840 1SL/20

