



MASTER TL5 High Efficiency Xtra Eco

MASTER TL5 HE Xtra Eco 25=28W/840 1SL

TL5 High Efficiency Xtra Eco lamp (tube diameter 16 mm) provides the ideal combination of extra-long life and extra energy savings via simple lamp-for-lamp replacement of TL5 HE lamps, without any compromise on the high lighting quality.

Warnings and Safety

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- To achieve lifetimes as published for 100% operation, dimming below 30% should not be applied.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp current (nom.)		0.170 A	
Cap base	G5 [G5]				
Features	na [Not Applicable]				
Light Technical		Controls and Dimming			
Colour Code	840 [CCT of 4000K]	Dimmable	Yes		
Luminous Flux	2,900 lm				
Colour designation	Cool White (CW)	Mechanical and Housing			
Correlated Colour Temperature	4000 K	Bulb shape	T5 [16 mm (T5)]		
Luminous efficacy (rated) (nom.)	103 lm/W				
Colour rendering index (CRI)	82	Approval and Application			
		Mercury (Hg) content (nom.)	3.0 mg		
		Energy consumption kWh/1,000 hours	28 kWh		
Operating and Electrical		Product Data			
Power Consumption	25.2 W	Order product name	MASTER TL5 HE Xtra Eco 25=28W/840 1SL		

MASTER TL5 High Efficiency Xtra Eco

Full product name	MASTER TL5 HE Xtra Eco 25=28W/840 1SL
Full EOC	871829166946300
Order code	66946300
Material no. (12 NC)	927994384055
Local order code	25840TL5ECOXTA
SAP numerator – quantity per pack	1


EAN/UPC – Product/Case	8718291669463
Numerator – packs per outer box	40
EAN/UPC - Case	8718291669470

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Xtra Eco 25=28W/840 1SL	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL5 HE Xtra Eco 25=28W/840 1SL

