



# MASTER TL-D Power Saver Set

## MST TL-D Power Sav Set 23=36W/865 1SL/25

The MASTER TL-D Power Saver Set is a perfect solution for upgrading your existing lighting installation with a special TL-D lamp with an intelligent starter. It offers considerable energy savings while maintaining the same lighting level and a better light quality. The MASTER TL-D Power Saver Set is easy to install, simply by changing the lamp and the starter. The benefits are huge in all current installations with TL-D lamps.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T8 [26 mm (T8)]
Light Technical		Approval and Application	
Color Code	865 [CCT of 6500K]	Mercury (Hg) Content (Nom)	2.0 mg
Color Designation	Cool Daylight	Energy Consumption kWh/1000 h	28 kWh
Correlated Color Temperature (Nom)	6500 K	Product Data	
Color rendering index (CRI)	82	Order product name	MST TL-D Power Sav Set 23=36W/865 1SL/25
Controls and Dimming		Full product name	MST TL-D Power Sav Set 23=36W/865 1SL/25
Dimmable	No	Full product code	872790091506800
		Order code	927997186502
		Material Nr. (12NC)	927997186502
		Numerator - Quantity Per Pack	1

MASTER TL-D Power Saver Set


EAN/UPC - Product/Case	8727900915068
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900915075

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Power Sav Set 23=36W/865 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - MST TL-D Power Sav Set 23=36W/865 1SL/25

