



# MASTER TL-D Power Saver Set

## MASTER TL-D Power Saver Set 37=58W/840 1SL/25

The MASTER TL-D Power Saver Set is a perfect solution for upgrading your existing lighting installation with a special TL-D lamp with an intelligent starter. It offers considerable energy savings while maintaining the same lighting level and a better light quality. The MASTER TL-D Power Saver Set is easy to install, simply by changing the lamp and the starter. The benefits are huge in all current installations with TL-D lamps.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Mechanical and Housing	
Cap base	G13 [Medium Bi-Pin Fluorescent]	Bulb shape	T8 [26 mm (T8)]
Light Technical		Approval and Application	
Colour Code	840 [CCT of 4000K]	Mercury (Hg) content (nom.)	2.0 mg
Colour designation	Cool White (CW)	Energy consumption kWh/1,000 hours	43 kWh
Correlated Colour Temperature	4000 K	Product Data	
Colour rendering index (CRI)	82	Order product name	MST TL-D Power Sav Set 37=58W/840 1SL/25
Controls and Dimming		Full product name	MASTER TL-D Power Saver Set 37=58W/840 1SL/25
Dimmable	No	Full EOC	872790091510500

# MASTER TL-D Power Saver Set

Order code	91510500
Material no. (12 NC)	927997284002
Local order code	58840TLDPSS1X1
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900915105


Numerator – packs per outer box	25
EAN/UPC – Case	8727900915112

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Power Sav Set 37=58W/840 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

## Photometric data



Spectral Power Distribution Colour - MST TL-D Power Sav Set 37=58W/840 1SL/25

