



MASTER TL-D Power Saver Set

MST TL-D Power Sav Set 37=58W/840 1SL/25

The MASTER TL-D Power Saver Set is a perfect solution for upgrading your existing lighting installation with a special TL-D lamp with an intelligent starter. It offers considerable energy savings while maintaining the same lighting level and a better light quality. The MASTER TL-D Power Saver Set is easy to install, simply by changing the lamp and the starter. The benefits are huge in all current installations with TL-D lamps.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | | Controls and Dimming | |
|------------------------------------|---------------------------------|-------------------------------|-----------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] | Dimmable | No |
| Light Technical | | Mechanical and Housing | |
| Color Code | 840 [CCT of 4000K] | Bulb Shape | T8 [26 mm (T8)] |
| Color Designation | Cool White (CW) | Approval and Application | |
| Correlated Color Temperature (Nom) | 4000 K | Mercury (Hg) Content (Nom) | 2.0 mg |
| Color rendering index (CRI) | 82 | Energy Consumption kWh/1000 h | 43 kWh |

MASTER TL-D Power Saver Set

| Product Data | |
|---------------------|--|
| Order product name | MST TL-D Power Sav Set 37=58W/840 1SL/25 |
| Full product name | MST TL-D Power Sav Set 37=58W/840 1SL/25 |
| Full product code | 872790091510500 |
| Order code | 927997284002 |
| Material Nr. (12NC) | 927997284002 |


| | |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900915105 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8727900915112 |

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---|---------|------------|------------|------------|------------|
| MST TL-D Power Sav Set 37=58W/840 1SL/25 | 28 mm | 1,500.0 mm | 1,507.1 mm | 1,504.7 mm | 1,514.2 mm |

Photometric data



Spectral Power Distribution Colour - MST TL-D Power Sav Set 37=58W/840 1SL/25

