



# MASTER TL-D Power Saver Set

## MASTER TL-D Power Saver Set 37=58W/865 1SL/25

The MASTER TL-D Power Saver Set is a perfect solution for upgrading your existing lighting installation with a special TL-D lamp with an intelligent starter. It offers considerable energy savings while maintaining the same lighting level and a better light quality. The MASTER TL-D Power Saver Set is easy to install, simply by changing the lamp and the starter. The benefits are huge in all current installations with TL-D lamps.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


| General Information           |                                 | Mechanical and Housing             |   |
|-------------------------------|---------------------------------|------------------------------------|---|
| Cap base                      | G13 [Medium Bi-Pin Fluorescent] | Bulb shape                         | T8 [26 mm (T8)]                               |
| Light Technical               |                                 | Approval and Application           |   |
| Colour Code                   | 865 [CCT of 6500K]              | Mercury (Hg) content (nom.)        | 2.0 mg  |
| Colour designation            | Cool Daylight                   | Energy consumption kWh/1,000 hours | 44 kWh  |
| Correlated Colour Temperature | 6500 K                          | Product Data                       |   |
| Colour rendering index (CRI)  | 82                              | Order product name                 | MST TL-D Power Sav Set 37=58W/865 1SL/25      |
| Controls and Dimming          |                                 | Full product name                  | MASTER TL-D Power Saver Set 37=58W/865 1SL/25 |
| Dimmable                      | No                              | Full EOC                           | 872790091512900                               |

MASTER TL-D Power Saver Set

|                                   |                |
|-----------------------------------|----------------|
| Order code                        | 91512900       |
| Material no. (12 NC)              | 927997286502   |
| Local order code                  | 58865TLDPSS1X1 |
| SAP numerator – quantity per pack | 1              |
| EAN/UPC – Product/Case            | 8727900915129  |


|                                 |               |
|---------------------------------|---------------|
| Numerator – packs per outer box | 25            |
| EAN/UPC – Case                  | 8727900915136 |

Dimensional drawing



| Product                                     | D (max) | A (max)    | B (max)    | B (min)    | C (max)    |
|---|---------|------------|------------|------------|------------|
| MST TL-D Power Sav Set<br>37=58W/865 1SL/25 | 28 mm   | 1,500.0 mm | 1,507.1 mm | 1,504.7 mm | 1,514.2 mm |

Photometric data



Spectral Power Distribution Colour - MST TL-D Power Sav Set 37=58W/865 1SL/25

