



# Actinic BL TL(-K) / TL-D(-K)

## Actinic BL TL MINI 4W/10 /10X25CC

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures (Nom)	8,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Actinic
UV Depreciation at 1000 h	25 %
UV Depreciation at 2000 h	35 %
UV Depreciation at 5000 h	17 %
Operating and Electrical	
Power Consumption	4.5 W


Lamp Current (Nom)	0.17 A
Voltage (Nom)	29 V
Voltage (Nom)	29 V
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	Actinic BL TL MINI 4W/10
Full product name	Actinic BL TL MINI 4W/10 /10X25CC

Actinic BL TL(-K) / TL-D(-K)

Full product code	871150095142727
Order code	95142727
Material Nr. (12NC)	928000001030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500951427


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500951441

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL MINI 4W/10	16 mm	135.9 mm	143 mm	140.6 mm	150.1 mm

Photometric data



Spectral Power Distribution Colour – Actinic BL TL MINI 4W/10

