



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL 11W/10

Tubular low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Mechanical and Housing	
Cap-Base	G5	Bulb Shape	T16
Useful Life (Nom)	2,000 h		
Light Technical		Approval and Application	
Color Code	10	Mercury (Hg) Content (Nom)	4.4 mg
Color Designation	Actinic		
Chromaticity Coordinate X (Nom)	230	UV	
Chromaticity Coordinate Y (Nom)	230	UV-A Radiation 100Hr (IEC)	2.0 W
UV Depreciation at 1000 h	40 %		
UV Depreciation at 2000 h	45 %	Product Data	
UV Depreciation at 500 h	30 %	Order product name	Actinic BL TL 11W/10
Operating and Electrical		Full product name	Actinic BL TL 11W/10
Power Consumption	11.5 W	Full product code	871150095145827
Lamp Current (Nom)	0.400 A	Local code description	TL11W10
Voltage (Nom)	34 V	Order code	928000601030
Voltage (Nom)	34 V	Material Nr. (12NC)	928000601030
		Local order code	TL11W10
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500951458

Actinic BL TL(-K) / TL-D(-K)


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500951472

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 11W/10	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

Photometric data



Spectral Power Distribution Colour - Actinic BL TL 11W/10

