



TL Mini Standard Colours

TL Mini 8W/54-765 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap-Base	G5	56 V	
Flux measurement reference	Sphere	Controls and Dimming	
Life to 50% Failures (Nom)	10,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	54-765	Bulb Shape	T5
Luminous Flux	335 lm	Approval and Application	
Color Designation	Cool Daylight	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.313	Mercury (Hg) Content (Max)	2.5 mg
Chromaticity Coordinate Y (Nom)	0.337	Mercury (Hg) Content (Nom)	4.4 mg
Correlated Color Temperature (Nom)	6500 K	Energy Consumption kWh/1000 h	8 kWh
Luminous Efficacy (rated) (Nom)	48 lm/W	EPREL Registration Number	423492
Color rendering index (CRI)	72	Product Data	
Operating and Electrical		Order product name	TL Mini 8W/54-765 FAM/10X25BOX
Power Consumption	7.1 W	Full product name	TL Mini 8W/54-765 FAM/10X25BOX
Lamp Current (Nom)	0.145 A	Full product code	871150071628627
Voltage (Nom)	56 V		

TL Mini Standard Colours

Order code	928001005440
Material Nr. (12NC)	928001005440
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500716286


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500716309

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/54-765 FAM/ 10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

Photometric data



Spectral Power Distribution Colour - TL Mini 8W/54-765 FAM/10X25BOX

