



TL Mini consumer products



TL Mini 13W/33-640 1PP/10

They come in different wattages and colors with moderate (/33) to good (/827) light quality.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|------------------------------------|-----------------|
| Cap-Base | G5 |
| Flux measurement reference | Sphere |
| Life to 50% Failures (Nom) | 8,000 hour(s) |
| Light Technical | |
| Color Code | 33-640 |
| Luminous Flux | 835 lm |
| Color Designation | Cool White (CW) |
| Chromaticity Coordinate X (Nom) | 0.38 |
| Chromaticity Coordinate Y (Nom) | 0.38 |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 71 lm/W |
| Color rendering index (CRI) | 59 |
| Operating and Electrical | |
| Power Consumption | 13.1 W |
| Lamp Current (Nom) | 0.170 A |

| Voltage (Nom) | 90 V |
|-------------------------------|---------------------------|
| Voltage (Nom) | 90 V |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Shape | T5 |
| Approval and Application | |
| Energy Efficiency Class | G |
| Mercury (Hg) Content (Max) | 2.5 mg |
| Mercury (Hg) Content (Nom) | 4.4 mg |
| Energy Consumption kWh/1000 h | 14 kWh |
| EPREL Registration Number | 423497 |
| Product Data | |
| Order product name | TL Mini 13W/33-640 1PP/10 |


TL Mini consumer products

| | |
|-------------------------------|---------------------------|
| Full product name | TL Mini 13W/33-640 1PP/10 |
| Full product code | 871150062698125 |
| Order code | 928001503313 |
| Material Nr. (12NC) | 928001503313 |
| Numerator - Quantity Per Pack | 1 |


| | |
|---------------------------------|---------------|
| EAN/UPC - Product/Case | 8711500626981 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8711500262110 |

Dimensional drawing

| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---------------------------|---------|----------|----------|----------|----------|
| TL Mini 13W/33-640 1PP/10 | 16 mm | 516.9 mm | 524.0 mm | 521.6 mm | 531.1 mm |



Photometric data



Spectral Power Distribution Colour - TL Mini 13W/33-640 1PP/10

