

TL Mini Standard Colours

TL Mini 13W/54-765 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)		90 V
Cap-Base	G5	Controls and Dimming		
Flux measurement reference	Sphere	Dimmable	Yes	
Life to 50% Failures (Nom)	8,000 hour(s)	Mechanical and Housing		
Light Technical		Bulb Shape	T5	
Color Code	54-765	Approval and Application		
Luminous Flux	740 lm	Energy Efficiency Class	G	
Color Designation	Cool Daylight	Mercury (Hg) Content (Max)	2.5 mg	
Chromaticity Coordinate X (Nom)	0.313	Mercury (Hg) Content (Nom)	4.4 mg	
Chromaticity Coordinate Y (Nom)	0.337	Energy Consumption kWh/1000 h	14 kWh	
Correlated Color Temperature (Nom)	6500 K	EPREL Registration Number	423499	
Luminous Efficacy (rated) (Nom)	57 lm/W	Product Data		
Color rendering index (CRI)	72	Order product name	TL Mini 13W/54-765 FAM/10X25BOX	
Operating and Electrical		Full product name	TL Mini 13W/54-765 FAM/10X25BOX	
Power Consumption	13.1 W	Full product code	871150071671227	
Lamp Current (Nom)	0.170 A			
Voltage (Nom)	90 V			

TL Mini Standard Colours

Order code	928001505440
Material Nr. (12NC)	928001505440
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500716712


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500716736

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 13W/54-765 FAM/ 10X25BOX	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

Photometric data



Spectral Power Distribution Colour - TL Mini 13W/54-765 FAM/10X25BOX

