



MASTER TL Mini Super 80



MASTER TL Mini Super 80 13W/840 1FM/10X25CC

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	8,000 hour(s)

Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	1,000 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	13.1 W
Lamp Current (Nom)	0.170 A
Voltage (Nom)	90 V

Voltage (Nom)	90 V
---------------	------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	14 kWh
EPREL Registration Number	423503


Product Data	
Order product name	MST TL Mini 13W/840 FAM/10X25BOX
Full product name	MASTER TL Mini Super 80 13W/840 1FM/10X25CC
Full product code	871150071685927

MASTER TL Mini Super 80

Order code	71685927
Material Nr. (12NC)	928001508450
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500716859


Numerator - Packs per outer box	250
EAN/UPC - Case	8711500716873

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL Mini 13W/840 FAM/ 10X25BOX	16 mm	516.9 mm	524.0 mm	521.6 mm	531.1 mm

Photometric data



Spectral Power Distribution Colour - MST TL Mini 13W/840 FAM/10X25BOX

