



Flexo Print

TL 80W/10-R SLV/25

Flexo print TL lamps emit almost all of their light (99.9%) in the useful UVA and visible blue wavebands – between 350 and 400 nm – and have peak intensity at 370 nm (except for the /03 version). This makes them ideal for flexo printing equipment and photopolymerization processes. In addition, the ‘R’ lamps in the family have an internal 200-degree reflector to further optimize the lamp’s overall efficiency.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
50% 故障条件下的使用寿命 (标称)	1,000 小时
有效寿命 (标称)	1,000 小时
灯技术	
颜色代码	10-R
颜色名称	紫外光 A
色度坐标 X (标称)	222
色度坐标 Y (标称)	210
1000 小时时的 UV 衰减	20 %
2000 小时时的 UV 衰减	30 %
500 小时时的 UV 衰减	10 %
操作和电气	
功耗	80 W


灯具电流 (标称)	0.83 A
电压 (标称)	110 V
电压 (标称)	110 V
机械和外壳	
灯泡外形	T38 [T 38 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	13.0 mg
UV	
紫外线 A 辐射 100 小时 (IEC)	20.5 W
产品数据	
订单产品名称	TL 80W/10-R SLV/25
完整的产品名称	TL 80W/10-R SLV/25

完整产品代码	871150061262540
订购代码	928005901029
材料编号 (12NC)	928005901029
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500612625


计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	8711500612632

二维绘图

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 80W/10-R SLV/25	40.5 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm



光度数据



Spectral Power Distribution Colour - TL 80W/10-R SLV/25

