



Flexo Print

TL 100W/10-R UV-A

Flexo print TL lamps emit almost all of their light (99.9%) in the useful UVA and visible blue wavebands – between 350 and 400 nm – and have peak intensity at 370 nm (except for the /03 version). This makes them ideal for flexo printing equipment and photopolymerization processes. In addition, the ‘R’ lamps in the family have an internal 200-degree reflector to further optimize the lamp’s overall efficiency.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
50% 故障条件下的使用寿命 (标称)	2,000 小时
有效寿命 (标称)	1,000 小时
灯技术	
颜色代码	10-R
颜色名称	紫外光 A
色度坐标 X (标称)	220
色度坐标 Y (标称)	200
1000 小时时的 UV 衰减	20 %
2000 小时时的 UV 衰减	30 %
500 小时时的 UV 衰减	10 %
操作和电气	
功耗	100 W


灯具电流 (标称)	0.97 A
电压 (标称)	122 V
电压 (标称)	122 V
机械和外壳	
灯泡外形	T38 [T 38 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	13.0 mg
UV	
紫外线 A 辐射 0 小时 (IEC)	28.0 W
紫外线 A 辐射 100 小时 (IEC)	26.0 W
产品数据	
订单产品名称	TL 100W/10-R UV-A

完整的产品名称	TL 100W/10-R UV-A
完整产品代码	871150061281640
订购代码	928006901029
材料编号 (12NC)	928006901029
计算器 - 每包数量	1


EAN/UPC - 产品/箱	8711500612816
计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	8711500612823

二维绘图

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 100W/10-R UV-A	40.5 mm	1,763.8 mm	1,770.9 mm	1,768.5 mm	1,778 mm



光度数据



Spectral Power Distribution Colour - TL 100W/10-R UV-A

