



Flexo Print

TL 140W/03

Flexo print TL lamps emit almost all of their light (99.9%) in the useful UVA and visible blue wavebands – between 350 and 400 nm – and have peak intensity at 370 nm (except for the /03 version). This makes them ideal for flexo printing equipment and photopolymerization processes. In addition, the 'R' lamps in the family have an internal 200-degree reflector to further optimize the lamp's overall efficiency.

安全提示

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
50% 故障条件下的使用寿命 (标称)	3,000 小时
灯技术	
颜色代码	03
颜色名称	超级光化
色度坐标 X (标称)	175
色度坐标 Y (标称)	45
1000 小时时的 UV 衰减	30 %
2000 小时时的 UV 衰减	40 %
500 小时时的 UV 衰减	20 %
操作和电气	
功耗	140 W
灯具电流 (标称)	1.46 A

电压 (标称)	118 V
电压 (标称)	118 V
机械和外壳	
灯泡外形	T38 [T 38 毫米]
UV	
紫外线 A 辐射 100 小时 (IEC)	1.00 W
产品数据	
订单产品名称	TL 140W/03
完整的产品名称	TL 140W/03
完整产品代码	871150072094840
订购代码	928012700303
材料编号 (12NC)	928012700303
计算器 - 每包数量	1

Flexo Print


EAN/UPC - 产品/箱	8711500720948
计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	8711500720955

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 140W/03	40.5 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

光度数据



Spectral Power Distribution Colour - TL 140W/03

