



Actinic BL TL(-K) / TL-D(-K)

ACTINIC BL TL-DK - 30W/10 1SL

Tubular low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | |
|---------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom) | 2,000 h |
| Useful Life (Nom) | 2,000 h |
| | |
| Light Technical | |
| Color Code | 10 |
| Color Designation | Actinic |
| Chromaticity Coordinate X (Nom) | 225 |
| Chromaticity Coordinate Y (Nom) | 230 |
| UV Depreciation at 1000 h | 25 % |
| UV Depreciation at 2000 h | 40 % |
| UV Depreciation at 500 h | 15 % |
| | |
| Operating and Electrical | |
| Power Consumption | 30 W |
| Lamp Current (Nom) | 0.805 A |
| Voltage (Nom) | 45 V |

| Voltage (Nom) | 45 V |
|-------------------------------|-------------------------------|
| | |
| Mechanical and Housing | |
| Bulb Shape | T26 [T 26mm] |
| | |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 8.0 mg |
| | |
| UV | |
| UV-A Radiation 100Hr (IEC) | 6.6 W |
| | |
| Product Data | |
| Order product name | ACTINIC BL TL-DK - 30W/10 1SL |
| Full product name | ACTINIC BL TL-DK - 30W/10 1SL |
| Full product code | 871150089346840 |
| Order code | 928019501029 |
| Material Nr. (12NC) | 928019501029 |
| Local order code | TLDK30W/10 |
| Numerator - Quantity Per Pack | 1 |

Actinic BL TL(-K) / TL-D(-K)


| | |
|---------------------------------|---------------|
| EAN/UPC - Product/Case | 8711500893468 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8711500893475 |

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|-------------------------------|---------|----------|----------|----------|----------|
| ACTINIC BL TL-DK - 30W/10 1SL | 28 mm | 437.4 mm | 444.5 mm | 442.1 mm | 451.6 mm |

Photometric data



Spectral Power Distribution Colour - ACTINIC BL TL-DK - 30W/10 1SL

