



Retail Sales T8

F15T8/COOL WHITE PLUS/18 ALTO SL 6


Energy Savings, extra long life, extra low mercury. T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	830 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	63
Operating and Electrical	
Power Consumption	15 W
Lamp Current (Nom)	0.335 A
Wattage Equivalent	15 W
Voltage (Nom)	55 V
Voltage (Nom)	55 V
Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	F15T8/COOL WHITE PLUS/18 ALTO SL 6
Full product name	F15T8/COOL WHITE PLUS/18 ALTO SL 6
Order code	928022803328
Material Nr. (12NC)	928022803328
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677392079
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677392074

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/COOL WHITE PLUS/18 ALTO SL 6	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data




Spectral Power Distribution Colour - F15T8/COOL WHITE PLUS/18 ALTO SL 6

Lifetime




Life Expectancy Diagram - F15T8/COOL WHITE PLUS/18 ALTO SL 6



Life Expectancy Diagram - F15T8/COOL WHITE PLUS/18 ALTO SL 6

Retail Sales T8

Lifetime



Lumen Maintenance Diagram - F15T8/COOL WHITE PLUS/18 ALTO SL 6

