



TL-D Standard Colours

TL-D 10W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom) | 5,000 hour(s) |
| Light Technical | |
| Color Code | 33-640 |
| Luminous Flux | 440 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4100 K |
| Color rendering index (CRI) | 60 |
| Operating and Electrical | |
| Power Consumption | 10 W |
| Lamp Current (Nom) | 0.230 A |
| Voltage (Nom) | 46 V |
| Voltage (Nom) | 46 V |

| Controls and Dimming | |
|---------------------------------|------------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Shape | T8 |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 8.0 mg |
| Product Data | |
| Order product name | TL-D 10W/33-640 1SL/25 |
| Full product name | TL-D 10W/33-640 1SL/25 |
| Full product code | 871150064128100 |
| Order code | 928024003331 |
| Material Nr. (12NC) | 928024003331 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500641281 |
| Numerator - Packs per outer box | 25 |

TL-D Standard Colours


| | |
|----------------|---------------|
| EAN/UPC - Case | 8711500641298 |
|----------------|---------------|

Dimensional drawing




| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|------------------------|---------|----------|----------|----------|----------|
| TL-D 10W/33-640 1SL/25 | 28 mm | 331.5 mm | 338.6 mm | 336.2 mm | 345.7 mm |

Photometric data




Spectral Power Distribution Colour - TL-D 10W/33-640 1SL/25

Lifetime



Life Expectancy Diagram - TL-D 10W/33-640 1SL/25



Life Expectancy Diagram - TL-D 10W/33-640 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 10W/33-640 1SL/25

