



# TL-D Blacklight Blue

## F15T8/BLACKLIGHT/18 BLB LF6PK

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	8,000 hour(s)
Useful Life (Nom)	5,000 hour(s)
Light Technical	
Color Code	108 [08 lead free glass]
Color Designation	Blacklight Blue
Operating and Electrical	
Power Consumption	15.9 W
Lamp Current (Nom)	0.310 A
Voltage (Nom)	54 V
Voltage (Nom)	54 V
Mechanical and Housing	
Bulb Shape	T26 [T 26mm]

Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
UV	
UV-A Radiation 100Hr (IEC)	3.0 W
Product Data	
Order product name	F15T8/BLACKLIGHT/18 BLB LF6PK
Full product name	F15T8/BLACKLIGHT/18 BLB LF6PK
Order code	157602
Material Nr. (12NC)	928024810821
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677157609
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677157604


# TL-D Blacklight Blue

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/BLACKLIGHT/18 BLB LF6PK	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

## Photometric data



Spectral Power Distribution Colour - F15T8/BLACKLIGHT/18 BLB LF6PK

