



TL-D Blacklight Blue

F15T8/BLACKLIGHT/18 BLB LF6PK

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T26 [T 26mm]
Life to 50% Failures (Nom)	8,000 hour(s)	Approval and Application	
Useful Life (Nom)	5,000 hour(s)	Mercury (Hg) Content (Nom)	5.0 mg
Light Technical		UV	
Color Code	108 [08 lead free glass]	UV-A Radiation 100Hr (IEC)	3.0 W
Color Designation	Blacklight Blue	Product Data	
Operating and Electrical		Order product name	F15T8/BLACKLIGHT/18 BLB LF6PK
Power Consumption	15.9 W	Full product name	F15T8/BLACKLIGHT/18 BLB LF6PK
Lamp Current (Nom)	0.310 A	Order code	157602
Voltage (Nom)	54 V	Material Nr. (12NC)	928024810821
Voltage (Nom)	54 V	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	046677157609

TL-D Blacklight Blue


Numerator - Packs per outer box	6
EAN/UPC - Case	50046677157604

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F15T8/BLACKLIGHT/18 BLB LF6PK	1-1/8 inch	17-1/4 inch	17-1/2 inch	17-7/16 inch	17-13/16 inch

Photometric data



Spectral Power Distribution Colour - F15T8/BLACKLIGHT/18 BLB LF6PK

