



# TL-D Standard Colours

## TL-D 30W/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Nominal lifetime	13,000 hour(s)		
Life to 50% Failures (Nom)	13,000 hour(s)	Mechanical and Housing	
		Bulb Shape	T8
Light Technical		Approval and Application	
Color Code	54-765	Mercury (Hg) Content (Nom)	5.0 mg
Luminous Flux	1,825 lm	Energy Consumption kWh/1000 h	36 kWh
Color Designation	Cool Daylight		
Correlated Color Temperature (Nom)	6200 K	Product Data	
Color rendering index (CRI)	72	Order product name	TL-D 30W/54-765 1SL/25
Operating and Electrical		Full product name	TL-D 30W/54-765 1SL/25
Power Consumption	30.0 W	Full product code	871150072263800
Lamp Current (Nom)	0.360 A	Order code	928025405482
Voltage (Nom)	98 V	Material Nr. (12NC)	928025405482
Voltage (Nom)	98 V	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500722638
		Numerator - Packs per outer box	25

# TL-D Standard Colours

EAN/UPC - Case


8711500722645

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 30W/54-765 1SL/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

## Photometric data




Spectral Power Distribution Colour - TL-D 30W/54-765 1SL/25

## Lifetime




Life Expectancy Diagram - TL-D 30W/54-765 1SL/25



Life Expectancy Diagram - TL-D 30W/54-765 1SL/25

## TL-D Standard Colours

### Lifetime



Lumen Maintenance Diagram - TL-D 30W/54-765 1SL/25

