



TL-E 80

TL-E 22W/840 1CT/20

Fluorescent lamps with a circular tube having a diameter of 26 mm


Product data

| General Information | |
|------------------------------------|--------------------|
| Cap-Base | G10Q [G10q] |
| Nominal lifetime | 8,000 hour(s) |
| Life to 50% Failures (Nom) | 13,000 hour(s) |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 1,285 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 59 lm/W |
| Color rendering index (CRI) | 80 |
| Operating and Electrical | |
| Power Consumption | 22 W |
| Lamp Current (Nom) | 0.400 A |
| Voltage (Nom) | 62 V |
| Voltage (Nom) | 62 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|---------------------|
| Bulb Shape | C-T29 |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 8 mg |
| Energy Consumption kWh/1000 h | 24 kWh |
| Product Data | |
| Order product name | TL-E 22W/840 1CT/20 |
| Full product name | TL-E 22W/840 1CT/20 |
| Full product code | 871150028665900 |
| Order code | 928026284074 |
| Material Nr. (12NC) | 928026284074 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500286659 |
| Numerator - Packs per outer box | 20 |
| EAN/UPC - Case | 8727900813579 |


TL-E 80

Dimensional drawing



| Product | D (max) | D (min) | E (min) | E (max) | I (min) | I (max) |
|---------------------|---------|---------|----------|----------|----------|----------|
| TL-E 22W/840 1CT/20 | 30.9 mm | 26.2 mm | 205.0 mm | 213.5 mm | 149.1 mm | 155.6 mm |

Photometric data



Spectral Power Distribution Colour - TL-E 22W/840 1CT/20

