



# MASTER TL-E Circular Super 80



## TL-E 32W/830 1CT/12

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	G10q	Power Consumption	32.8 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.450 A
Life to 50% Failures (Nom)	13,000 hour(s)	Voltage (Nom)	81 V
Light Technical		Voltage (Nom)	81 V
Color Code	830 [CCT of 3000K]	Controls and Dimming	
Luminous Flux	2,375 lm	Dimmable	Yes
Color Designation	Warm White (WW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.44	Bulb Shape	C-T29
Chromaticity Coordinate Y (Nom)	0.403	Approval and Application	
Correlated Color Temperature (Nom)	3000 K	Energy Efficiency Class	G
Luminous Efficacy (rated) (Nom)	74 lm/W	Mercury (Hg) Content (Max)	8 mg
Color rendering index (CRI)	80	Mercury (Hg) Content (Nom)	8 mg

# MASTER TL-E Circular Super 80

Energy Consumption kWh/1000 h	33 kWh
EPREL Registration Number	423508
<b>Product Data</b>	
Order product name	TL-E 32W/830 1CT/12
Full product name	TL-E 32W/830 1CT/12
Full product code	871150055967815
Order code	928026383070


Material Nr. (12NC)	928026383070
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559678
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500620682

## Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/830 1CT/12	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

## Photometric data



Spectral Power Distribution Colour - TL-E 32W/830 1CT/12

