



MASTER TL-E Circular Super 80

TL-E 32W/840 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in ‘human’ applications such as schools, offices, shops and homes, and for lighting of residential areas.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G10Q [G10q]
标称使用寿命	8,000 小时
50% 故障条件下的使用寿命 (标称)	13,000 小时
灯技术	
颜色代码	840 [CCT of 4000K]
光通量	2,375 lm
颜色名称	冷白色 (CW)
相关色温 (标称)	4000 K
光效 (额定) (标称)	74 lm/W
显色指数 (CRI)	80
操作和电气	
功耗	32.0 W
灯具电流 (标称)	0.450 A


电压 (标称)	81 V
电压 (标称)	81 V
控制和调光	
可调光	是
机械和外壳	
灯泡外形	C-T9 [C-T9 29 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	8 mg
能耗 kWh/1000 h	35 kWh
产品数据	
订单产品名称	TL-E 32W/840 1CT/20
完整的产品名称	TL-E 32W/840 1CT/20

MASTER TL-E Circular Super 80

完整产品代码	871150055968500
订购代码	928026384074
材料编号 (12NC)	928026384074
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500559685


计算器 - 每个外包装箱中的包数	20
EAN/UPC - 案例	8727900813609

二维绘图



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/840 1CT/20	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

光度数据



Spectral Power Distribution Colour - TL-E 32W/840 1CT/20

