



TL-E LIFEMAX Super 80 JIS

TL-E 40W/865 JIS 1CT/12


Low-pressure mercury discharge lamps with a circular 29 mm tube, complied with Japanese Industrial Standard

Product data

General Information		Mechanical and Housing	
Cap-Base	G10Q [G10q]	Bulb Shape	C-T9 [C-T9 29 mm]
Light Technical		Product Data	
Color Code	865 [CCT of 6500K]	Order product name	TL-E 40W/865 JIS 1CT/12
Luminous Flux	2,950 lm	Full product name	TL-E 40W/865 JIS 1CT/12
Color Designation	Cool Daylight	Full product code	871150028464800
Correlated Color Temperature (Nom)	6500 K	Order code	928026886529
Luminous Efficacy (rated) (Nom)	74 lm/W	Material Nr. (12NC)	928026886529
Color rendering index (CRI)	80	Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	8711500284648
Power Consumption	38.0 W	Numerator - Packs per outer box	12
Lamp Current (Nom)	0.425 A	EAN/UPC - Case	8711500286901
Voltage (Nom)	103 V		
Voltage (Nom)	103 V		
Controls and Dimming			
Dimmable	No		

TL-E LIFEMAX Super 80 JIS

Dimensional drawing



Product	D (max)	D (min)	E (max)	I (min)	I (max)
TL-E 40W/865 JIS 1CT/12	30.8 mm	27.1 mm	381 mm	309.0 mm	321.0 mm

