



# MASTER TL-E Circular Super 80



TL-E 40W/865 1CT/12

Low-pressure mercury discharge lamps with a circular 26 mm tube

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G10q
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	3,070 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	0.313
Chromaticity Coordinate Y (Nom)	0.337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	78 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	40.8 W
Lamp Current (Nom)	0.420 A
Voltage (Nom)	110 V


Voltage (Nom)	110 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	C-T29
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	8 mg
Mercury (Hg) Content (Nom)	8 mg
Energy Consumption kWh/1000 h	41 kWh
EPREL Registration Number	423513
Product Data	
Order product name	TL-E 40W/865 1CT/12
Full product name	TL-E 40W/865 1CT/12
Full product code	872790084057500

# MASTER TL-E Circular Super 80

Order code	84057500
Material Nr. (12NC)	928027486570
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900840575

Numerator - Packs per outer box	12
EAN/UPC - Case	8727900840582

## Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 40W/865 1CT/12	30.9 mm	27.1 mm	393.7 mm	406.4 mm	341.0 mm	347.7 mm

