



TL-M Rapid Start Standard Colours

TL-M RS 40W/54-765 1SL/25

The TL-M RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating and an external ignition strip. It is suitable for situations where low temperatures and high humidity require fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	2,500 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	63 lm/W
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	39.5 W
Lamp Current (Nom)	0.430 A
Voltage (Nom)	101 V


Voltage (Nom)	101 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12 [38 mm (T12)]
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	47 kWh
Product Data	
Order product name	TL-M RS 40W/54-765 1SL/25
Full product name	TL-M RS 40W/54-765 1SL/25
Full product code	871150072441040

TL-M Rapid Start Standard Colours

Order code	928030505471
Material Nr. (12NC)	928030505471
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500724410


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500724427

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-M RS 40W/54-765 1SL/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - TL-M RS 40W/54-765 1SL/25

