



TL-M Rapid Start Super 80

TL-M RS Super 80 65W/830 1SL/25

The TL-M RS (Rapid Start) Super 80 lamp (tube diameter 38 mm) offers more lumens per watt and better color rendering than TL standard colors. The lamp has an external silicon coating and an external ignition strip. It is suitable for situations where low temperatures and high humidity require fast and stable ignition. Rapid Start lamps can be ignited without a starter.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	110 V	
Life to 50% Failures (Nom)	13,000 hour(s)	Voltage (Nom)	
		110 V	
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	5,100 lm	Mechanical and Housing	
Color Designation	Warm White (WW)	Bulb Shape	T12 [38 mm (T12)]
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	80 lm/W	Mercury (Hg) Content (Nom)	8.0 mg
Color rendering index (CRI)	85	Energy Consumption kWh/1000 h	74 kWh
Operating and Electrical		Product Data	
Power Consumption	64.0 W	Order product name	TL-M RS Super 80 65W/830 1SL/25
Lamp Current (Nom)	0.670 A		

TL-M Rapid Start Super 80


Full product name	TL-M RS Super 80 65W/830 1SL/25
Full product code	871150072516540
Order code	928031008371
Material Nr. (12NC)	928031008371
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711500725165
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500725172

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-M RS Super 80 65W/830 1SL/25	40.5 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data



Spectral Power Distribution Colour - TL-M RS Super 80 65W/830 1SL/25

