



# TL10 Plus

## T10 PLUS 40W/765 1SL/25

The T10 Plus tubular fluorescent lamp line is available in 20W and 40W and is suitable for new installations, as well as replacement in existing installations. They work in conjunction with electromagnetic ballasts (Conventional and Quick Start) and electronic ballasts. Recommended for all types of installations, they deliver the reliability and guarantee of Philips applications.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	765 [CCT of 6500K]
Luminous Flux	2,500 lumen
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	40 W
Lamp Current (Nom)	0.42 A
Voltage (Nom)	112 V
Voltage (Nom)	112 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T10 [32 mm]
Approval and Application	
Mercury (Hg) Content (Nom)	8.5 mg
Product Data	
Full product code	871869652942300
Order product name	T10 PLUS 40W/765 1SL/25
Order code	928034705402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928034705402
Full product name	T10 PLUS 40W/765 1SL/25
EAN/UPC - Case	8718696529430
EAN/UPC - Product/Case	8718696529423


TL10 Plus

Dimensional drawing



Product
T10 PLUS 40W/765 1SL/25

Photometric data



Spectral Power Distribution Colour - T10 PLUS 40W/765 1SL/25

