



TL-S

TL-S 20W/840 SLV/25

The TL-S lamp (tube diameter 38 mm) has an internal ignition strip that ensures instant start. The lamp offers a well-defined ignition without a starter, also at low temperatures. It is suitable for situations with low switching frequency and where color rendering is not important. The R18s lamp cap at each end of the lamp requires a special lampholder.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	R18S [R18s]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	1,060 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	55 lm/W
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	19.4 W
Lamp Current (Nom)	0.385 A
Voltage (Nom)	58 V


Voltage (Nom)	58 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12 [38 mm (T12)]
Approval and Application	
Mercury (Hg) Content (Nom)	12 mg
Energy Consumption kWh/1000 h	24 kWh
Product Data	
Order product name	TL-S 20W/840 SLV/25
Full product name	TL-S 20W/840 SLV/25
Full product code	871150061936540
Order code	928035008405

TL-S

Material Nr. (12NC)	928035008405
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500619365
Numerator - Packs per outer box	25


EAN/UPC - Case	8711500619372
----------------	---------------

Dimensional drawing



Product	D (max)	A (min)	A (max)	B (max)	B (min)	C (min)	C (max)
TL-S	40.5 mm	571.9	573.9	583.1 mm	580.5	588.8	591.4
20W/840		mm	mm		mm	mm	mm
SLV/25							

Photometric data



Spectral Power Distribution Colour - TL-S 20W/840 SLV/25

