



# TL-X XL

## TL-X XL 40W/33-640 SLV/25

单针式荧光灯，直径为 38 mm

### 安全提示

· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

一般信息	
底盖	FA6 [FA6]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	26,000 小时

灯技术	
颜色代码	33-640
光通量	2,300 lm
颜色名称	冷白色 (CW)
色度坐标 X (标称)	0.38
色度坐标 Y (标称)	0.38
相关色温 (标称)	4000 K
光效 (额定) (标称)	58 lm/W
显色指数 (CRI)	60

操作和电气	
功耗	40.0 W
灯具电流 (标称)	0.430 A
电压 (标称)	103 V
电压 (标称)	103 V

控制和调光	
可调光	是

机械和外壳	
灯泡外形	T12 [38 毫米 (T12)]


审批和申请	
能效等级	G
汞 (Hg) 含量 (最高)	12 mg
汞 (Hg) 含量 (标称)	12.0 mg
能耗 kWh/1000 h	40 kWh
EPREL 注册号	423515

产品数据	
订单产品名称	TL-X XL 40W/33-640 SLV/25
完整的产品名称	TL-X XL 40W/33-640 SLV/25
完整产品代码	871150026137340
订购代码	928037903332
材料编号 (12NC)	928037903332
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500261373

# TL-X XL


计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	8711500261380

## 二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 40W/33-640 SLV/25	40.5 mm	1,183.5 mm	1,202 mm	1,198.5 mm	1,220.5 mm

## 光度数据



Spectral Power Distribution Colour - TL-X XL 40W/33-640 SLV/25

