



# TL-D U



## TL-D U 58W/840

This fluorescent lamp with a U-shaped tube enables the creation of compact luminaires. Often used for sign lighting and residential lighting, e.g. in post-top lanterns.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	2G13 [2G13]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	7,500 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	5,200 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	81
Operating and Electrical	
Power Consumption	59.9 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	115 V


Voltage (Nom)	115 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	U-T8 [U 26 mm]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	8 mg
Mercury (Hg) Content (Nom)	7 mg
Energy Consumption kWh/1000 h	60 kWh
EPREL Registration Number	423518
Product Data	
Order product name	TL-D U 58W/840
Full product name	TL-D U 58W/840
Full product code	872790086006100

TL-D U

Order code	928038684002
Material Nr. (12NC)	928038684002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900860061


Numerator - Packs per outer box	12
EAN/UPC - Case	8727900860078

Dimensional drawing



Product	D (max)	D (min)	A (max)	A (min)	E (min)	E (max)
TL-D U 58W/840	27 mm	23 mm	759 mm	749 mm	90 mm	94 mm

Photometric data



Spectral Power Distribution Colour - TL-D U 58W/840

