



# TUV T8

## TUV 25W 1SL/25

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

### 安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

### 产品数据

一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
有效寿命 ( 标称 )	9,000 小时
灯技术	
颜色代码	TUV
颜色名称	- [未指定]
有效寿命下的衰减	15 %
操作和电气	
功耗	25 W
灯具电流 ( 标称 )	0.612 A
电压 ( 标称 )	48 V


电压 ( 标称 )	48 V
机械和外壳	
灯泡外形	T26 [T 26 毫米]
审批和申请	
汞 (Hg) 含量 ( 标称 )	2.0 mg
UV	
100 小时下的紫外线 C 辐射	7.3 W
产品数据	
订单产品名称	TUV 25W 1SL/25
完整的产品名称	TUV 25W 1SL/25

完整产品代码	871150064161840
订购代码	928039404005
材料编号 (12NC)	928039404005
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500641618


计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	8711500641625

二维绘图

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 25W 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm



光度数据



Spectral Power Distribution Colour - TUV 25W 1SL/25

