



MASTER TL-D 90 De Luxe

MASTER TL-D 90 De Luxe 18W/940 1SL/10

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	940 [CCT of 4000K]
Luminous Flux	1,200 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	65.2 lm/W
Color rendering index (CRI)	91
Operating and Electrical	
Power Consumption	18.0 W
Lamp Current (Nom)	0.360 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	1.7 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Order product name	MASTER TL-D 90 De Luxe 18W/940 SLV/10
Full product name	MASTER TL-D 90 De Luxe 18W/940 1SL/10
Full product code	871150088839625
Order code	88839625
Material Nr. (12NC)	928043594081
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500888396
Numerator - Packs per outer box	10

MASTER TL-D 90 De Luxe


EAN/UPC - Case	8711500888402
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 18W/940 SLV/10	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 18W/940 SLV/10

Lifetime




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 18W/940 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 De Luxe 18W/940 SLV/10

MASTER TL-D 90 De Luxe

Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 18W/940 SLV/10

