



# MASTER TL-D 90 De Luxe



## MASTER TL-D 90 De Luxe 18W/952 1SL/10

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Flux measurement reference	Sphere		
Life to 50% Failures (Nom)	15,000 hour(s)	Mechanical and Housing	
		Bulb Shape	T8
Light Technical		Approval and Application	
Color Code	952	Energy Efficiency Class	G
Luminous Flux	1,150 lm	Mercury (Hg) Content (Nom)	1.7 mg
Color Designation	Daylight	Energy Consumption kWh/1000 h	19 kWh
Chromaticity Coordinate X (Nom)	0.34	EPREL Registration Number	423520
Chromaticity Coordinate Y (Nom)	0.351		
Correlated Color Temperature (Nom)	5200 K	Product Data	
Luminous Efficacy (rated) (Nom)	62.5 lm/W	Order product name	MASTER TL-D 90 De Luxe 18W/952 SLV/10
Color rendering index (CRI)	92	Full product name	MASTER TL-D 90 De Luxe 18W/952 1SL/10
Operating and Electrical		Full product code	871150088843325
Power Consumption	18.4 W	Order code	88843325
Lamp Current (Nom)	0.360 A	Material Nr. (12NC)	928043595081
		Numerator - Quantity Per Pack	1

# MASTER TL-D 90 De Luxe


EAN/UPC - Product/Case	8711500888433
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500888440

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 18W/952 SLV/10	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 18W/952 SLV/10

## Lifetime




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 18W/952 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 De Luxe 18W/952 SLV/10

# MASTER TL-D 90 De Luxe

## Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 18W/952 SLV/10

