



MASTER TL-D 90 De Luxe

MASTER TL-D 90 De Luxe 18W/965 SLV/10

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	965 [CCT of 6500K]
Luminous Flux	1,150 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	0.313
Chromaticity Coordinate Y (Nom)	0.337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	62.5 lm/W
Color rendering index (CRI)	93
Operating and Electrical	
Power Consumption	18.4 W
Lamp Current (Nom)	0.360 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.7 mg
Energy Consumption kWh/1000 h	19 kWh
EPREL Registration Number	423521
Product Data	
Order product name	MASTER TL-D 90 De Luxe 18W/965 SLV/10
Full product name	MASTER TL-D 90 De Luxe 18W/965 SLV/10
Full product code	871150088846425
Order code	928043596581
Material Nr. (12NC)	928043596581
Numerator - Quantity Per Pack	1

MASTER TL-D 90 De Luxe


EAN/UPC - Product/Case	8711500888464
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500888471

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 18W/965 SLV/10	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 18W/965 SLV/10

Lifetime




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 18W/965 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 De Luxe 18W/965 SLV/10

MASTER TL-D 90 De Luxe

Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 18W/965 SLV/10

