

PHILIPS

Lighting



MASTER TL-D 90 De Luxe (豪华型)

MASTER TL-D 90 De Luxe 18W/965 SLV/10

低压汞放电灯，配备管状 26 毫米的封装

安全提示

· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般信息		控制和调光	
底座	G13 [Medium Bi-Pin Fluorescent]	可调光	是
光通量测量参考	Sphere		
50% 故障条件下的使用寿命 (标称)	15,000 小时		
灯技术		机械和外壳	
颜色代码	965 [CCT of 6500K]	灯泡外形	T8 [26 毫米 (T8)]
光通量	1,150 lm		
颜色名称	冷日光		
色度坐标 X (标称)	0.313		
色度坐标 Y (标称)	0.337		
相关色温 (标称)	6500 K		
光效 (额定) (标称)	62.5 lm/W		
显色指数 (CRI)	93		
操作和电气		审批和申请	
功耗	18.4 W	能效等级	G
灯具电流 (标称)	0.360 A	汞 (Hg) 含量 (标称)	1.7 mg
		能耗 kWh/1000 h	19 kWh
		EPREL 注册号	423521
		产品数据	
		订单产品名称	MASTER TL-D 90 De Luxe 18W/965 SLV/10
		完整的产品名称	MASTER TL-D 90 De Luxe 18W/965 SLV/10
		完整产品代码	871150088846425
		订购代码	928043596581
		材料编号 (12NC)	928043596581
		计算器 - 每包数量	1

MASTER TL-D 90 De Luxe (豪华型)


EAN/UPC - 产品/箱	8711500888464
计算器 - 每个外包装箱中的包数	10
EAN/UPC - 案例	8711500888471

二维绘图





Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 18W/965 SLV/10	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

光度数据



Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 18W/965 SLV/10

寿命




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 18W/965 SLV/10

Life Expectancy Diagram - MASTER TL-D 90 De Luxe 18W/965 SLV/10

MASTER TL-D 90 De Luxe (豪华型)

寿命



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 18W/965 SLV/10

