



MASTER TL-D 90 Graphica

MASTER TL-D 90 Graphica 18W/952 SLV/10

低压汞放电灯，配备管状 26 毫米的封装。

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	8,000 小时
灯技术	
颜色代码	952
光通量	960 lm
颜色名称	日光
色度坐标 X (标称)	0.34
色度坐标 Y (标称)	0.351
相关色温 (标称)	5200 K
光效 (额定) (标称)	52.2 lm/W
显色指数 (CRI)	95
操作和电气	
功耗	18.4 W
灯具电流 (标称)	0.360 A

控制和调光	
可调光	是
机械和外壳	
灯泡外形	T8 [26 毫米 (T8)]
审批和申请	
能效等级	G
汞 (Hg) 含量 (标称)	1.7 mg
能耗 kWh/1000 h	19 kWh
EPREL 注册号	423522
产品数据	
订单产品名称	MASTER TL-D 90 Graphica 18W/952 SLV/10
完整的产品名称	MASTER TL-D 90 Graphica 18W/952 SLV/10
完整产品代码	871150088850125
订购代码	928043795081
材料编号 (12NC)	928043795081
计算器 - 每包数量	1

MASTER TL-D 90 Graphica


EAN/UPC - 产品/箱	8711500888501
计算器 - 每个外包装箱中的包数	10
EAN/UPC - 案例	8711500888518

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 Graphica 18W/952 SLV/10	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

光度数据




Spectral Power Distribution Colour - MASTER TL-D 90 Graphica 18W/952 SLV/10

寿命




Life Expectancy Diagram - MASTER TL-D 90 Graphica 18W/952 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 Graphica 18W/952 SLV/10

MASTER TL-D 90 Graphica

寿命



Lumen Maintenance Diagram - MASTER TL-D 90 Graphica 18W/952 SLV/10

