



MASTER TL-D 90 De Luxe (豪华型)

MASTER TL-D 90 De Luxe 36W/952 SLV/10

低压汞放电灯，配备管状 26 毫米的封装

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	15,000 小时
灯技术	
颜色代码	952
光通量	2,850 lm
颜色名称	日光
色度坐标 X (标称)	0.34
色度坐标 Y (标称)	0.351
相关色温 (标称)	5200 K
光效 (额定)(标称)	77.4 lm/W
显色指数 (CRI)	92
操作和电气	
功耗	36.8 W
灯具电流 (标称)	0.440 A

控制和调光	
可调光	是
机械和外壳	
灯泡外形	T8 [26 毫米 (T8)]
审批和申请	
能效等级	G
汞 (Hg) 含量 (标称)	1.7 mg
能耗 kWh/1000 h	37 kWh
EPREL 注册号	423525
产品数据	
订单产品名称	MASTER TL-D 90 De Luxe 36W/952 SLV/10
完整的产品名称	MASTER TL-D 90 De Luxe 36W/952 SLV/10
完整产品代码	871150088860025
订购代码	928044595081
材料编号 (12NC)	928044595081
计算器 - 每包数量	1

MASTER TL-D 90 De Luxe (豪华型)


EAN/UPC - 产品/箱	8711500888600
计算器 - 每个外包装箱中的包数	10
EAN/UPC - 案例	8711500888617

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 36W/952 SLV/10	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

光度数据




Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 36W/952 SLV/10

寿命




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 36W/952 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 De Luxe 36W/952 SLV/10

MASTER TL-D 90 De Luxe (豪华型)

寿命



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 36W/952 SLV/10

