



# MASTER TL-D 90 De Luxe (豪华型)

## MASTER TL-D 90 De Luxe 58W/952 SLV/10

低压汞放电灯，配备管状 26 毫米的封装

### 安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据


| 一般信息                |                                 |
|---------------------|---------------------------------|
| 底盖                  | G13 [Medium Bi-Pin Fluorescent] |
| 光通量测量参考             | Sphere                          |
| 50% 故障条件下的使用寿命 (标称) | 15,000 小时                       |
| 灯技术                 |                                 |
| 颜色代码                | 952                             |
| 光通量                 | 4,550 lm                        |
| 颜色名称                | 日光                              |
| 色度坐标 X (标称)         | 0.34                            |
| 色度坐标 Y (标称)         | 0.351                           |
| 相关色温 (标称)           | 5200 K                          |
| 光效 (额定) (标称)        | 76.1 lm/W                       |
| 显色指数 (CRI)          | 92                              |
| 操作和电气               |                                 |
| 功耗                  | 59.8 W                          |
| 灯具电流 (标称)           | 0.670 A                         |

| 控制和调光          |                                       |
|----------------|---------------------------------------|
| 可调光            | 是                                     |
| 机械和外壳          |                                       |
| 灯泡外形           | T8 [26 毫米 (T8)]                       |
| 审批和申请          |                                       |
| 能效等级           | G                                     |
| 汞 (Hg) 含量 (标称) | 1.7 mg                                |
| 能耗 kWh/1000 h  | 60 kWh                                |
| EPREL 注册号      | 423530                                |
| 产品数据           |                                       |
| 订单产品名称         | MASTER TL-D 90 De Luxe 58W/952 SLV/10 |
| 完整的产品名称        | MASTER TL-D 90 De Luxe 58W/952 SLV/10 |
| 完整产品代码         | 871150088871625                       |
| 订购代码           | 928045095081                          |
| 材料编号 (12NC)    | 928045095081                          |
| 计算器 - 每包数量     | 1                                     |

MASTER TL-D 90 De Luxe (豪华型)


|                  |               |
|------------------|---------------|
| EAN/UPC - 产品/箱   | 8711500888716 |
| 计算器 - 每个外包装箱中的包数 | 10            |
| EAN/UPC - 案例     | 8711500888723 |

二维绘图




| Product                                  | D (max) | A (max)    | B (max)    | B (min)    | C (max)    |
|------------------------------------------|---------|------------|------------|------------|------------|
| MASTER TL-D 90 De Luxe<br>58W/952 SLV/10 | 28 mm   | 1,500.0 mm | 1,507.1 mm | 1,504.7 mm | 1,514.2 mm |

光度数据




Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 58W/952 SLV/10

寿命




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 58W/952 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 De Luxe 58W/952 SLV/10

MASTER TL-D 90 De Luxe (豪华型)

寿命



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 58W/952 SLV/10

