



# MASTER TL-D 90 Graphica

## MASTER TL-D 90 Graphica 58W/952 1SL/10

This TL-D lamp has excellent color rendering which makes it very suitable for the graphical and printing industry to check the quality of printed material.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Lamp Current (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		0.670 A
Flux measurement reference	Sphere	Controls and Dimming	
Life to 50% Failures (Nom)	8,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	952	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux	3,640 lm	Approval and Application	
Color Designation	Daylight	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.34	Mercury (Hg) Content (Nom)	1.7 mg
Chromaticity Coordinate Y (Nom)	0.351	Energy Consumption kWh/1000 h	60 kWh
Correlated Color Temperature (Nom)	5200 K	EPREL Registration Number	423532
Luminous Efficacy (rated) (Nom)	61.1 lm/W	Product Data	
Color rendering index (CRI)	97	Order product name	MASTER TL-D 90 Graphica 58W/952 SLV/10
Operating and Electrical		Full product name	MASTER TL-D 90 Graphica 58W/952 1SL/10
Power Consumption	59.6 W	Full product code	871150088875425

# MASTER TL-D 90 Graphica

Order code	88875425
Material Nr. (12NC)	928045295081
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500888754


Numerator - Packs per outer box	10
EAN/UPC - Case	8711500888761

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 Graphica 58W/952 SLV/10	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 Graphica 58W/952 SLV/10

## Lifetime




Life Expectancy Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10

# MASTER TL-D 90 Graphica

## Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10

