



MASTER TL-D 90 Graphica



MASTER TL-D 90 Graphica 58W/952 1SL/10

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	8,000 h
Light Technical	
Colour Code	952
Luminous Flux	3,640 lm
Colour designation	Daylight
Chromaticity Coordinate X (Nom)	0.34
Chromaticity Coordinate Y (Nom)	0.351
Correlated Colour Temperature	5200 K
Luminous efficacy (rated) (nom.)	61.1 lm/W
Colour rendering index (CRI)	97
Operating and Electrical	
Power Consumption	59.6 W
Lamp current (nom.)	0.670 A


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	T8 [26 mm (T8)]
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.7 mg
Energy consumption kWh/1,000 hours	60 kWh
EPREL registration number	423532
Product Data	
Order product name	MASTER TL-D 90 Graphica 58W/952 SLV/10
Full product name	MASTER TL-D 90 Graphica 58W/952 1SL/10
Full EOC	871150088875425
Order code	88875425
Material no. (12 NC)	928045295081
Local order code	58950GP

MASTER TL-D 90 Graphica

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500888754
Numerator – packs per outer box	10


EAN/UPC – Case	8711500888761
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 Graphica 58W/952 SLV/10	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 Graphica 58W/952 SLV/10

Lifetime




Life Expectancy Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10

MASTER TL-D 90 Graphica

Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10

