



MASTER TL-D 90 Graphica

MASTER TL-D 90 Graphica 58W/952 SLV/10

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Flux measurement reference	Sphere		
Life to 50% Failures (Nom)	8,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	952	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux	3,640 lm		
Color Designation	Daylight	Approval and Application	
Chromaticity Coordinate X (Nom)	0.34	Energy Efficiency Class	G
Chromaticity Coordinate Y (Nom)	0.351	Mercury (Hg) Content (Nom)	1.7 mg
Correlated Color Temperature (Nom)	5200 K	Energy Consumption kWh/1000 h	60 kWh
Luminous Efficacy (rated) (Nom)	61.1 lm/W	EPREL Registration Number	423532
Color rendering index (CRI)	97		
Operating and Electrical		Product Data	
Power Consumption	59.6 W	Order product name	MASTER TL-D 90 Graphica 58W/952 SLV/10
Lamp Current (Nom)	0.670 A	Full product name	MASTER TL-D 90 Graphica 58W/952 SLV/10
		Full product code	871150088875425
		Order code	928045295081
		Material Nr. (12NC)	928045295081
		Numerator - Quantity Per Pack	1

MASTER TL-D 90 Graphica


EAN/UPC - Product/Case	8711500888754
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500888761

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 Graphica 58W/952 SLV/10	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 Graphica 58W/952 SLV/10

Lifetime




Life Expectancy Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10

MASTER TL-D 90 Graphica

Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 Graphica 58W/952 SLV/10

