



TL-D Colored

TLD 18W/15 (RED) 25PK

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	15,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	150	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux	25 lm		
Color Designation	Red (HO)	Approval and Application	
		Mercury (Hg) Content (Nom)	13.0 mg
		Energy Consumption kWh/1000 h	26 kWh
Operating and Electrical		Product Data	
Power Consumption	18.0 W	Order product name	TL-D Colored 18W Red 1SL/25
Lamp Current (Nom)	0.360 A	Full product name	TLD 18W/15 (RED) 25PK
Voltage (Nom)	59 V	Full product code	871150072684140
Voltage (Nom)	59 V	Order code	203059
		Material Nr. (12NC)	928048001505

TL-D Colored

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500726841
Numerator - Packs per outer box	25


EAN/UPC - Case	8711500726858
----------------	---------------

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 18W Red 1SL/25	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

Photometric data



Spectral Power Distribution Colour - TL-D Colored 18W Red 1SL/25

