



TL-D 标准颜色

TL-D 18W/29-530 1SL/25

低压汞放电灯，带有一个 26mm 的管状包层。

安全提示

· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般信息	
底座	G13 [Medium Bi-Pin Fluorescent]
50% 故障条件下的使用寿命 (标称)	13,000 小时
灯技术	
颜色代码	29-530
光通量	1,250 lm
颜色名称	暖白色 (WW)
相关色温 (标称)	2900 K
显色指数 (CRI)	51
操作和电气	
功耗	18.0 W
灯具电流 (标称)	0.360 A
电压 (标称)	59 V
电压 (标称)	59 V
控制和调光	
可调光	是

机械和外壳	
灯泡外形	T8 [26 毫米 (T8)]
审批和申请	
汞 (Hg) 含量 (标称)	8.0 mg
产品数据	
订单产品名称	TL-D 18W/29-530 1SL/25
完整的产品名称	TL-D 18W/29-530 1SL/25
完整产品代码	872790085834100
订购代码	928048002953
材料编号 (12NC)	928048002953
计算器 - 每包数量	1
EAN/UPC - 产品/箱	6923410798098
计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	6923410798463


TL-D 标准颜色

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/29-530 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

光度数据




Spectral Power Distribution Colour - TL-D 18W/29-530 1SL/25

寿命




Life Expectancy Diagram - TL-D 18W/29-530 1SL/25



Life Expectancy Diagram - TL-D 18W/29-530 1SL/25

TL-D 标准颜色

寿命



Lumen Maintenance Diagram - TL-D 18W/29-530 1SL/25

