



MASTER TL-D Reflex

MASTER TL-D Reflex 36W/840 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% failures (nom.)	15,000 h
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	3,350 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	93.1 lm/W
Colour rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	36.0 W
Lamp current (nom.)	0.440 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Reflector

Bulb shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) content (nom.)	5.0 mg
Energy consumption kWh/1,000 hours	42 kWh
Product Data	
Order product name	MST TL-D Reflex 36W/840 1 SLV/25
Full product name	MASTER TL-D Reflex 36W/840 1SL/25
Full EOC	871150055953140
Order code	55953140
Material no. (12 NC)	928048408479
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500559531
Numerator – packs per outer box	25
EAN/UPC – Case	8711500559548


MASTER TL-D Reflex

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Reflex 36W/840 1 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MST TL-D Reflex 36W/840 1 SLV/25

Lifetime




Life Expectancy Diagram - MST TL-D Reflex 36W/840 1 SLV/25



Life Expectancy Diagram - MST TL-D Reflex 36W/840 1 SLV/25

MASTER TL-D Reflex

Lifetime



Lumen Maintenance Diagram - MST TL-D Reflex 36W/840 1 SLV/25

