



MASTER TL-D Reflex

MST TL-D Reflex 36W/840 1 SLV/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	3,350 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	93.1 lm/W
Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	36.0 W
Lamp Current (Nom)	0.440 A


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Reflector
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	42 kWh
Product Data	
Order product name	MST TL-D Reflex 36W/840 1 SLV/25
Full product name	MST TL-D Reflex 36W/840 1 SLV/25
Full product code	871150055953140
Order code	928048408479
Material Nr. (12NC)	928048408479
Local order code	9280-484-08478

MASTER TL-D Reflex

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559531
Numerator - Packs per outer box	25


EAN/UPC - Case	8711500559548
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Reflex 36W/840 1 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MST TL-D Reflex 36W/840 1 SLV/25

Lifetime




Life Expectancy Diagram - MST TL-D Reflex 36W/840 1 SLV/25



Life Expectancy Diagram - MST TL-D Reflex 36W/840 1 SLV/25

MASTER TL-D Reflex

Lifetime



Lumen Maintenance Diagram - MST TL-D Reflex 36W/840 1 SLV/25

