



MASTER TL-D Reflex

MST TL-D Reflex 36W/840 1 SLV/25

The MASTER TL-D Reflex lamp directs most of the light to where you need it, thanks to an internal reflector. This results in having the same lighting level while using only half the number of lamps in the luminaire. It is therefore extremely suitable for use in luminaires with only a simple reflector or without any.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	3,350 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	93.1 lm/W
Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	36.0 W
Lamp Current (Nom)	0.440 A

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Reflector
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	42 kWh
Product Data	
Order product name	MST TL-D Reflex 36W/840 1 SLV/25
Full product name	MST TL-D Reflex 36W/840 1 SLV/25
Full product code	871150055953140
Order code	928048408479
Material Nr. (12NC)	928048408479
Numerator - Quantity Per Pack	1

MASTER TL-D Reflex


EAN/UPC - Product/Case	8711500559531
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500559548

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Reflex 36W/840 1 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MST TL-D Reflex 36W/840 1 SLV/25

Lifetime



Life Expectancy Diagram - MST TL-D Reflex 36W/840 1 SLV/25



Life Expectancy Diagram - MST TL-D Reflex 36W/840 1 SLV/25

MASTER TL-D Reflex

Lifetime

Lumen Maintenance Diagram - MST TL-D Reflex 36W/840 1 SLV/25

