



TL-D Colored

TL-D Colored 36W Yellow 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

Güvenlik ve uyarılar

- Lamba kırılmasının sağlığını üzerinde herhangi bir olumsuz etkisi olmayacağını söylemek pek de mümkün değildir. Bir lamba kırıldığında, odayı 30 dakika süreyle havalandırın ve kırık parçaları tercihen eldiven kullanarak toplayın. Bunları ağız kapalı bir plastik torbaya koyun ve geri dönüşüm için size en yakın atık toplama merkezine götürün. Elektrikli süpürge kullanmayın.

Ürün veri


Genel Bilgiler		Kontroller ve Dim Etme	
Kapak Tabanı	G13 [Medium Bi-Pin Fluorescent]	Dim Edilebilir	Evet
%50 Arızaya Kadar Kullanım Ömrü (Nom)	15.000 h		
Işık Teknik Ayrıntıları		Mekanik ve Muhafaza	
Renk Kodu	160	Lamba Biçimi	T8 [26 mm (T8)]
Işık Akısı	1.580 lm		
Renk Kodlaması	Sarı	Onay ve Uygulama	
		Cıva (Hg) İçeriği (Nom)	13,0 mg
		Enerji Tüketimi kWh/1000 sa.	44 kWh
Çalıştırma ve Elektrik		Ürün Verileri	
Güç Tüketimi	36,0 W	Sipariş ürün adı	TL-D Colored 36W Yellow 1SL/25
Lamba Akımı (Nom)	0,440 A	Tam ürün adı	TL-D Colored 36W Yellow 1SL/25
Voltaj (Nom)	103 V	Tam ürün kodu	871150072751040
Voltaj (Nom)	103 V	Sipariş kodu	72751040
		Malzeme No. (12NC)	928048501605

TL-D Colored

Numeratör - Paket Başına Miktar	1
EAN/UPC - Ürün/Kutu	8711500727510
Numeratör - Büyük kutu başına paket sayısı	25


EAN/UPC - Kutu	8711500727527
----------------	---------------

Boyutlu çizim



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 36W Yellow 1SL/25	28,0 mm	1.199,4 mm	1.206,5 mm	1.204,1 mm	1.213,6 mm

Fotometrik bilgi



Spectral Power Distribution Colour - TL-D Colored 36W Yellow 1SL/25

